





**Pushbutton indicator switch 10 AX 250 V~with upright rocker
Universal 1-way/2-way switch**



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	0124 201	1/5	01	4010337052715
 pure white matt	0124 27	1/5	01	4010337029403
 anthracite	0124 28	1/5	11	4010337029427
 colour aluminium	0124 26	1	11	4010337029410
 black matt	0124 005	1	11	4010337037958
 stainless steel	0124 600	1	11	4010337021230

Technical data

Installation depth: 28 mm

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Rated output
- LEDi/CFLi: 100 W

Notes

- Can also be connected to be illuminated.

Scope of supply

- A neon lamp element 230 V~, 1.5 mA is included in the scope of supply.
