









**Pushbutton switch 10 AX 250 V~ with rocker
Universal 1-way/2-way switch**



| Specification | Order No. | Packing unit | PS | EAN |
|-------------------------------------------------------------------------------------------------------|-----------|--------------|----|---------------|
|  cream white glossy | 0126 01 | 1/5 | 01 | 4010337126010 |
|  pure white glossy | 0126 03 | 1/5 | 01 | 4010337126034 |
|  pure white matt | 0126 27 | 1/5 | 01 | 4010337126270 |
|  anthracite | 0126 28 | 1/5 | 11 | 4010337126287 |
|  colour aluminium | 0126 26 | 1/5 | 11 | 4010337126263 |
|  black matt | 0126 005 | 1/5 | 11 | 4010337037965 |
|  grey matt | 0126 015 | 1/5 | 11 | 4010337077145 |
|  stainless steel | 0126 600 | 1/5 | 11 | 4010337021742 |

Technical data

Installation depth: 28 mm

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Illustrations are similar and may deviate from originals.

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Rated output
- LEDi/CFLi:

100 W
