







Gira E1 cover frame
pure white glossy



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  1-gang | 0211 150 | 10 | 6.53 | 01 | 4010337126119 |
|  2-gang | 0212 150 | 10 | 8.96 | 01 | 4010337126126 |
|  2-gang, without crossbar | 1002 150 | 10 | 8.96 | 01 | 4010337126133 |
|  3-gang | 0213 150 | 1/5 | 16.36 | 01 | 4010337126140 |
|  4-gang | 0214 150 | 1/5 | 26.42 | 01 | 4010337126157 |
|  5-gang | 0215 150 | 1/5 | 40.32 | 01 | 4010337126164 |

Features

- Shatter-proof.

Notes

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.