







## Gira Standard 55 cover frame pure white glossy



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 1-gang	0211 03	10/100	2.78	21	4010337211037
 2-gang	0212 03	10/100	4.75	21	4010337212034
 2-gang, without crossbar	1002 03	10	3.51	01	4010337001607
 3-gang	0213 03	10/100	8.38	01	4010337213031
 4-gang	0214 03	1/5	14.49	01	4010337214038
 5-gang	0215 03	1/5	23.83	01	4010337215035

### Features

- Shatter-proof.

### Notes

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.