







Gira E1 cover frame anthracite



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  1-gang | 0211 152 | 10 | 6.86 | 11 | 4010337125969 |
|  2-gang | 0212 152 | 10 | 9.91 | 11 | 4010337125976 |
|  2-gang, without crossbar | 1002 152 | 1 | 9.91 | 11 | 4010337125983 |
|  3-gang | 0213 152 | 1/5 | 17.15 | 11 | 4010337125990 |
|  4-gang | 0214 152 | 1/5 | 27.64 | 11 | 4010337126027 |
|  5-gang | 0215 152 | 1/5 | 42.13 | 11 | 4010337126041 |

Features

- Shatter-proof.

Notes

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.