







Gira Standard 55 cover frame pure white matt



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  1-gang | 0211 04 | 10/100 | 2.78 | 21 | 4010337211044 |
|  2-gang | 0212 04 | 10/100 | 4.75 | 21 | 4010337212041 |
|  2-gang, without crossbar | 1002 04 | 10 | 3.51 | 01 | 4010337002048 |
|  3-gang | 0213 04 | 10/100 | 8.38 | 01 | 4010337213048 |
|  4-gang | 0214 04 | 1/5 | 14.49 | 01 | 4010337214045 |
|  5-gang | 0215 04 | 1/5 | 23.83 | 01 | 4010337215042 |

Features

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.

Notes

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.