


**Gira Standard 55 cover frame
cream white glossy**



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  1-gang | 0211 01 | 10/100 | 2.69 | 21 | 4010337211013 |
|  2-gang | 0212 01 | 10/100 | 4.61 | 21 | 4010337212010 |
|  2-gang, without crossbar | 1002 01 | 10 | 3.40 | 01 | 4010337002017 |
|  3-gang | 0213 01 | 10/100 | 8.12 | 01 | 4010337213017 |
|  4-gang | 0214 01 | 1/5 | 14.04 | 01 | 4010337214014 |
|  5-gang | 0215 01 | 1/5 | 23.09 | 01 | 4010337215011 |

Features

- Shatter-proof.

Notes

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.