






Gira E2 cover frame colour aluminium



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  1-gang | 0211 25 | 10/100 | 10.58 | 11 | 4010337211259 |
|  2-gang | 0212 25 | 10 | 16.07 | 11 | 4010337212256 |
|  2-gang, without crossbar | 1002 25 | 10 | 16.07 | 11 | 4010337002253 |
|  3-gang | 0213 25 | 1/5 | 26.43 | 11 | 4010337213253 |
|  4-gang | 0214 25 | 1/5 | 42.93 | 11 | 4010337214250 |
|  5-gang | 0215 25 | 1/5 | 65.32 | 11 | 4010337215257 |

Notes

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.