


## Electronic potentiometer insert for 1–10 V control input Switching function



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	0309 00	1/5	43.63	02	4010337309000

### Features

- Electronic potentiometer with switching function for electronic ballasts or Tronic transformers with 1 – 10 V control input.
- Pressing the operating knob switches the electronic ballasts on and off.
- Rotating adjusts the brightness.

### Technical data

Rated voltage: AC 230 V, 50/60 Hz

1 – 10 V interface

- Control voltage: 0.5 to 10 V
- Control current: max. 50 mA

Switching current

- Ohmic: 6 A
- Capacitive: 6 A (70 µF)

Installation depth: 32 mm

Connections

- maximum: 4 mm<sup>2</sup>

Ambient temperature: +5 °C to +45 °C

### Scope of supply

- Fuse is included in the scope of supply.