







## Gira Standard 55 cover frame pure white glossy



| Specification  | Order No. | Packing unit | PS | EAN           |
|--|-----------|--------------|----|---------------|
|  1-gang                    | 0211 03   | 10/100       | 21 | 4010337211037 |
|  2-gang                   | 0212 03   | 10/100       | 21 | 4010337212034 |
|  2-gang, without crossbar | 1002 03   | 10           | 01 | 4010337001607 |
|  3-gang                   | 0213 03   | 10/100       | 01 | 4010337213031 |
|  4-gang                   | 0214 03   | 1/5          | 01 | 4010337214038 |
|  5-gang                   | 0215 03   | 1/5          | 01 | 4010337215035 |

### Features

- Shatter-proof.

### Notes

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.