

## Lighting element for surface-mounted housing



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	1067 01	1/5	20.25	02	4010337105169
pure white glossy	1067 03	1/5	20.25	02	4010337107088

## Features

- The white LEDs project a light corridor downwards. This produces indirect orientation light that also avoids bothersome glare in bedrooms.

## Technical data

Rated voltage:	AC 230 V, 50 Hz
Power consumption:	0.05 W / 1.65 mA
Light intensity:	0.2 cd
Ambient temperature:	-15 °C to +40 °C