










**Gira Standard 55 cover frame with inscription space
cream white glossy**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 1-gang	1091 01	10	6.20	01	4010337091011
 2-gang horizontal	1092 01	10	11.50	01	4010337092018
 2-gang vertical	1102 01	10	11.50	01	4010337102014
 3-gang horizontal	1093 01	1/5	18.11	01	4010337093015
 3-gang vertical	1103 01	1/5	18.11	01	4010337103011
 4-gang horizontal	1094 01	1/5	26.39	01	4010337094012
 4-gang vertical	1114 01	1	26.39	01	4010337008903
 5-gang horizontal	1095 01	1	39.67	01	4010337095019
 5-gang vertical	1115 01	1	39.67	01	4010337115014

Features

- Shatter-proof.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
-

Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-