










**Gira Standard 55 cover frame with inscription space
pure white glossy**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 1-gang	1091 03	10	6.20	01	4010337091035
 2-gang horizontal	1092 03	10	11.50	01	4010337092032
 2-gang vertical	1102 03	10	11.50	01	4010337102038
 3-gang horizontal	1093 03	10	18.11	01	4010337093039
 3-gang vertical	1103 03	1/5	18.11	01	4010337103035
 4-gang horizontal	1094 03	1/5	26.39	01	4010337094036
 4-gang vertical	1114 03	1/5	26.39	01	4010337008910
 5-gang horizontal	1095 03	1/5	39.67	01	4010337095033
 5-gang vertical	1115 03	1/5	39.67	01	4010337115038

Features

- Shatter-proof.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
-

Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-