










**Gira E2 cover frame with inscription space
black matt**



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|---|-----------|--------------|------------------------|----|---------------|
|  1-gang | 1091 09 | 10 | 14.03 | 11 | 4010337036746 |
|  2-gang horizontal | 1092 09 | 10 | 22.98 | 11 | 4010337036814 |
|  2-gang vertical | 1102 09 | 10 | 22.98 | 11 | 4010337036807 |
|  3-gang horizontal | 1093 09 | 1/5 | 36.75 | 11 | 4010337036852 |
|  3-gang vertical | 1103 09 | 1/5 | 36.75 | 11 | 4010337036845 |
|  4-gang horizontal | 1094 09 | 1/5 | 56.66 | 11 | 4010337036890 |
|  4-gang vertical | 1114 09 | 1 | 56.66 | 11 | 4010337036883 |
|  5-gang horizontal | 1095 09 | 1/5 | 82.50 | 11 | 4010337036920 |
|  5-gang vertical | 1115 09 | 1 | 82.50 | 11 | 4010337036913 |

Features

- Shatter-proof.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
-

Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-