










Gira E2 cover frame with inscription space black matt



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 1-gang	1091 09	10	14.48	11	4010337036746
 2-gang horizontal	1092 09	10	23.72	11	4010337036814
 2-gang vertical	1102 09	10	23.72	11	4010337036807
 3-gang horizontal	1093 09	1/5	37.93	11	4010337036852
 3-gang vertical	1103 09	1/5	37.93	11	4010337036845
 4-gang horizontal	1094 09	1/5	58.47	11	4010337036890
 4-gang vertical	1114 09	1	58.47	11	4010337036883
 5-gang horizontal	1095 09	1/5	85.14	11	4010337036920
 5-gang vertical	1115 09	1	85.14	11	4010337036913

Features

- Shatter-proof.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
 - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
-

Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-