










## Gira E2 cover frame with inscription space anthracite



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 1-gang	1091 23	10	10.61	11	4010337084044
 2-gang horizontal	1092 23	10	17.35	11	4010337084099
 2-gang vertical	1102 23	10	17.35	11	4010337089148
 3-gang horizontal	1093 23	1/5	28.35	11	4010337084174
 3-gang vertical	1103 23	1/5	28.35	11	4010337084211
 4-gang horizontal	1094 23	1	42.72	11	4010337084259
 4-gang vertical	1114 23	1/5	42.72	11	4010337084297
 5-gang horizontal	1095 23	1	61.19	11	4010337084372
 5-gang vertical	1115 23	1	61.19	11	4010337084334

## Features

- Shatter-proof.
  - Spray-proof.
  - Frames with transparent view window for inscription.
  - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
  - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- 

## Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-