










**Gira Standard 55 cover frame with inscription space
pure white matt**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 1-gang	1091 27	10	6.40	01	4010337091271
 2-gang horizontal	1092 27	10	11.87	01	4010337092278
 2-gang vertical	1102 27	10	11.87	01	4010337102274
 3-gang horizontal	1093 27	1	18.68	01	4010337093275
 3-gang vertical	1103 27	1/5	18.68	01	4010337103271
 4-gang horizontal	1094 27	1/5	27.23	01	4010337094272
 4-gang vertical	1114 27	1	27.23	01	4010337008927
 5-gang horizontal	1095 27	1	40.94	01	4010337095279
 5-gang vertical	1115 27	1	40.94	01	4010337115274

Features

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
-

Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-