











**Gira E2 cover frame with inscription space  
pure white glossy**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 1-gang	1091 29	10	10.30	01	4010337084068
 2-gang horizontal	1092 29	10	16.35	01	4010337084129
 2-gang vertical	1102 29	10	16.35	01	4010337084150
 3-gang horizontal	1093 29	1/5	27.54	01	4010337084198
 3-gang vertical	1103 29	1/5	27.54	01	4010337084235
 4-gang horizontal	1094 29	1/5	41.44	01	4010337084273
 4-gang vertical	1114 29	1	41.44	01	4010337084310
 5-gang horizontal	1095 29	1/5	59.36	01	4010337084396
 5-gang vertical	1115 29	1/5	59.36	01	4010337084358

## Features

- Shatter-proof.
  - Spray-proof.
  - Frames with transparent view window for inscription.
  - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
  - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- 

## Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-