











**Gira E2 cover frame with inscription space  
grey matt**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 1-gang	1091 37	10	14.48	11	4010337082590
 2-gang horizontal	1092 37	10	23.72	11	4010337082651
 2-gang vertical	1102 37	10	23.72	11	4010337082699
 3-gang horizontal	1093 37	1/5	37.93	11	4010337082668
 3-gang vertical	1103 37	1/5	37.93	11	4010337082729
 4-gang horizontal	1094 37	1	58.47	11	4010337082675
 4-gang vertical	1114 37	1/5	58.47	11	4010337082873
 5-gang horizontal	1095 37	1/5	85.14	11	4010337082682
 5-gang vertical	1115 37	1/5	85.14	11	4010337082880

## Features

- Shatter-proof.
  - Spray-proof.
  - Frames with transparent view window for inscription.
  - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
  - Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- 

## Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-