










**Gira E2 cover frame with inscription space
pure white glossy**



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|---|-----------|--------------|------------------------|----|---------------|
|  1-gang | 1091 29 | 10 | 9.98 | 01 | 4010337084068 |
|  2-gang horizontal | 1092 29 | 10 | 15.85 | 01 | 4010337084129 |
|  2-gang vertical | 1102 29 | 10 | 15.85 | 01 | 4010337084150 |
|  3-gang horizontal | 1093 29 | 1/5 | 26.69 | 01 | 4010337084198 |
|  3-gang vertical | 1103 29 | 1/5 | 26.69 | 01 | 4010337084235 |
|  4-gang horizontal | 1094 29 | 1/5 | 40.15 | 01 | 4010337084273 |
|  4-gang vertical | 1114 29 | 1 | 40.15 | 01 | 4010337084310 |
|  5-gang horizontal | 1095 29 | 1/5 | 57.52 | 01 | 4010337084396 |
|  5-gang vertical | 1115 29 | 1/5 | 57.52 | 01 | 4010337084358 |

Features

- Shatter-proof.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
-

Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-