










**Gira Standard 55 cover frame with inscription space  
pure white matt**



| Specification   | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|---|-----------|--------------|------------------------|----|---------------|
|  1-gang             | 1091 27   | 10           | 6.20                   | 01 | 4010337091271 |
|  2-gang horizontal | 1092 27   | 10           | 11.50                  | 01 | 4010337092278 |
|  2-gang vertical   | 1102 27   | 10           | 11.50                  | 01 | 4010337102274 |
|  3-gang horizontal | 1093 27   | 1            | 18.11                  | 01 | 4010337093275 |
|  3-gang vertical   | 1103 27   | 1/5          | 18.11                  | 01 | 4010337103271 |
|  4-gang horizontal | 1094 27   | 1/5          | 26.39                  | 01 | 4010337094272 |
|  4-gang vertical   | 1114 27   | 1            | 26.39                  | 01 | 4010337008927 |
|  5-gang horizontal | 1095 27   | 1            | 39.67                  | 01 | 4010337095279 |
|  5-gang vertical   | 1115 27   | 1            | 39.67                  | 01 | 4010337115274 |

## Features

- Shatter-proof.
  - Spray-proof.
  - Frames with transparent view window for inscription.
  - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
- 

## Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-