










**Gira E2 cover frame with inscription space  
colour aluminium**



| Specification   | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|---|-----------|--------------|------------------------|----|---------------|
|  1-gang             | 1091 25   | 10           | 14.48                  | 11 | 4010337084051 |
|  2-gang horizontal | 1092 25   | 10           | 23.72                  | 11 | 4010337084112 |
|  2-gang vertical   | 1102 25   | 10           | 23.72                  | 11 | 4010337084143 |
|  3-gang horizontal | 1093 25   | 1/5          | 37.93                  | 11 | 4010337084181 |
|  3-gang vertical   | 1103 25   | 1/5          | 37.93                  | 11 | 4010337084228 |
|  4-gang horizontal | 1094 25   | 1/5          | 58.47                  | 11 | 4010337084266 |
|  4-gang vertical   | 1114 25   | 1/5          | 58.47                  | 11 | 4010337084303 |
|  5-gang horizontal | 1095 25   | 1            | 85.14                  | 11 | 4010337084389 |
|  5-gang vertical   | 1115 25   | 1/5          | 85.14                  | 11 | 4010337084341 |

## Features

- Shatter-proof.
- Spray-proof.
- Frames with transparent view window for inscription.
- Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.

---

## Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-