

## LED signal light 230 V~



| Specification  | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|--|-----------|--------------|------------------------|----|---------------|
|  red / green | 1171 00   | 1            | 102.73                 | 02 | 4010337049289 |

### Features

- The signal light can be used for simple signalling for treatment rooms, conference rooms, and hotel rooms, for example.
- The full insert surface of 55 x 55 mm is evenly illuminated, divided into the upper half for the colour red, and the lower half for the colour green.
- Both halves can be activated separately, e.g. by using a series switch.

### Technical data

|                          |                     |
|--------------------------|---------------------|
| Rated voltage:           | AC 230 V, 50 Hz     |
| Power consumption:       | 1.0 W/5.6 VA        |
| Light intensity          |                     |
| - red:                   | 0.1 cd              |
| - green:                 | 0.3 cd              |
| Installation depth:      | 30 mm               |
| Connection cross section |                     |
| - maximum:               | 2.5 mm <sup>2</sup> |
| Ambient temperature:     | 0 °C to +40 °C      |
| - Dimensions             | W 55 x H 55 mm      |
| Insert area:             |                     |

### Scope of supply

- Two inscription labels "Bitte warten" / "Bitte eintreten" and "Do not disturb" / "Make up room" are included.