


LED signal light 230 V~



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 red / green	1171 00	1	102.73	02	4010337049289

Features

- The signal light can be used for simple signalling for treatment rooms, conference rooms, and hotel rooms, for example.
- The full insert surface of 55 x 55 mm is evenly illuminated, divided into the upper half for the colour red, and the lower half for the colour green.
- Both halves can be activated separately, e.g. by using a series switch.

Technical data

Rated voltage:	AC 230 V, 50 Hz
Power consumption:	1.0 W/5.6 VA
Light intensity	
- red:	0.1 cd
- green:	0.3 cd
Installation depth:	30 mm
Connection cross section	
- maximum:	2.5 mm ²
Ambient temperature:	0 °C to +40 °C

Scope of supply

- Two inscription labels "Bitte warten" / "Bitte eintreten" and "Do not disturb" / "Make up room" are included.

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Dimensions in mm

Insert area:

B 55

H 55
