




## Surface-mounted video home station 7



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 pure white glossy	1209 03	1	690.70	10	4010337053422
 black matt	1209 005	1	690.70	10	4010337053408

### Features

- Fully pre-assembled unit including a 17.78 cm (7") TFT colour display and convenient speakerphone function.
- Full-surface glass front with touch functionality.
- Direct wall mounting or wall mounting with flush-mounted device box or cavity wall box.
- Mounting with base foot for placement on items of furniture.

### Technical data

Power supply:	DC 26 V ± 2 V (by 2-wire bus)
Connections	
- 2-wire bus:	2 x plug terminal
- Additional power supply:	2 x plug terminal
- Floor-call button:	2 x plug terminal
Display	
- Diagonal:	17.78 cm (= 7")
- Colour system:	PAL
- Resolution:	1024 x 600 pixels
microSD card	
- Type:	SDHC
- SDHC memory capacity:	32 GB
- File system:	FAT 32
Ambient temperature:	-5 °C to +50 °C

# GIRA Data sheet

catalogue.gira.com

© Copyright by  
Gira Giersiepen GmbH & Co. KG  
All rights reserved

www.gira.com

## Dimensions in mm

B 181

H 123

T 24

---