




## Surface-mounted video home station 7



| Specification  | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|--|-----------|--------------|------------------------|----|---------------|
|  pure white glossy | 1209 03   | 1            | 690.70                 | 10 | 4010337053422 |
|  black matt       | 1209 005  | 1            | 690.70                 | 10 | 4010337053408 |

### Features

- Fully pre-assembled unit including a 17.78 cm (7") TFT colour display and convenient speakerphone function.
- Full-surface glass front with touch functionality.
- Direct wall mounting or wall mounting with flush-mounted device box or cavity wall box.
- Mounting with base foot for placement on items of furniture.

### Technical data

Power supply: DC 26 V  $\pm$  2 V (by 2-wire bus)

#### Connections

- 2-wire bus: 2 x plug terminal
- Additional power supply: 2 x plug terminal
- Floor-call button: 2 x plug terminal

#### Display

- Diagonal: 17.78 cm (= 7")
- Colour system: PAL
- Resolution: 1024 x 600 pixels

#### microSD card

- Type: SDHC
- SDHC memory capacity: 32 GB
- File system: FAT 32

Ambient temperature: -5 °C to +50 °C

# GIRA Data sheet

catalogue.gira.com

© Copyright by  
Gira Giersiepen GmbH & Co. KG  
All rights reserved

www.gira.com

## Dimensions in mm

B 181

H 123

T 24

---