




## Door station, 3-gang TX\_44



| Specification  | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|--|-----------|--------------|------------------------|----|---------------|
|  pure white        | 1261 66   | 1            | 321.33                 | 18 | 4010337261667 |
|  anthracite       | 1261 67   | 1            | 330.70                 | 18 | 4010337261674 |
|  colour aluminium | 1261 65   | 1            | 330.70                 | 18 | 4010337261650 |

### Features

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX\_44 switch range.
- Modular design, therefore easy installation and expandability with further components such as call buttons, info module, colour camera, Keyless In.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man commissioning with simple commissioning procedure.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Call-button illumination with LED technology, light colour white. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Acknowledgement tone when call button is pressed.
- Voice volume adjustable.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and frame removal.
- Professional inscription by the Gira inscription service [www.beschriftung.gira.de](http://www.beschriftung.gira.de) or the Gira inscription software.
- Binary input for connecting a zero-voltage push button (NO contact) as a call button.
- Call button, 3-gang

### Technical data

Power supply: via the 2-wire bus

Bus coupler connections  
- 2-wire bus: 2 x screw terminal

Illustrations are similar and may deviate from originals.  
Prices valid for United Kingdom with prices valid 08/24.

|                            |                     |
|----------------------------|---------------------|
| - Additional power supply: | 2 x screw terminal  |
| - Binary input:            | 2 x screw terminal  |
| - Connection cable:        | 2 x connector strip |
| - Video:                   | 1 x connector strip |

#### Speech insert connections

|                     |                     |
|---------------------|---------------------|
| - Connection cable: | 2 x connector strip |
|---------------------|---------------------|

|                      |                  |
|----------------------|------------------|
| Ambient temperature: | -25 °C to +70 °C |
|----------------------|------------------|

|                   |      |
|-------------------|------|
| Protection class: | IP44 |
|-------------------|------|

|                     |       |
|---------------------|-------|
| Installation depth: | 30 mm |
|---------------------|-------|

---

#### Notes

- If only two call buttons are required, please use the call-button cover plate for call button, 3-gang.

---

#### Dimensions in mm

|              |      |      |
|--------------|------|------|
| Name plates: | B 62 | H 18 |
|--------------|------|------|

---