


## Call button, 1 gang for door station TX\_44



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 Program-neutral	1262 00	1	153.15	18	4010337262008

### Features

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX\_44 switch range.
- Modular design, allowing easy installation and expandability.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- The door station can be expanded with an additional call button (up to 14 call button inserts, 1- or 3-gang can be connected to one door station).
- Call-button illumination with LED technology, light colour white. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate can be replaced without tools and without removing the frame.
- Professional inscription by the Gira inscription service [www.beschriftung.gira.de](http://www.beschriftung.gira.de) or the Gira inscription software.

### Technical data

Power supply:	via connection cable
Connecting the connection cable:	2 x connector strip
Protection class:	IP44
Ambient temperature:	-25 °C to +70 °C
Installation depth:	30 mm
Dimensions	
- Name plate:	W 62 x H 62 mm