




## Surface-mounted door station, 1 gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 pure white	1266 66	1	268.43	18	4010337266662
 anthracite	1266 67	1	278.15	18	4010337266679
 colour aluminium	1266 65	1	278.15	18	4010337266655

## Features

- Fully pre-assembled surface-mounted door station for vertical surface-mounted installation. This facilitates fast and clean installation.
- In the design of the Gira TX\_44 design line.
- Torsion-resistant surface-mounted housing due to aluminium profile.
- Frame made of shatter-proof thermoplastic with high resistance to ultraviolet light as well as a scratch-resistant, care-free surface.
- Theft protection ensured by screws with hexalobular socket.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man commissioning with simple commissioning procedure.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Acknowledgement tone when call button is pressed.
- Voice volume adjustable.
- White call-button illumination with LED technology. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and frame removal.
- Professional inscription by the Gira inscription service [www.beschriftung.gira.de](http://www.beschriftung.gira.de) or the Gira inscription software.
- Low installation height of just 19 mm.

## Technical data

Power supply:	DC 26 V ± 2 V (by 2-wire bus)
Connections	
- 2-wire bus:	2 x screw terminal

- Additional power supply: 2 x screw terminal

Protection class: IP44

Ambient temperature: -25 °C to +70 °C

---

## Dimensions in mm

Door station, 1-gang:	B 110	H 181	T 19
Name plate:	B 62	H 62	T -

---