


Power supply DC 24 V 300 mA



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 DRA	1296 00	1	87.05	18	4010337296003

Features

- Power supply DC 24 V for supplying power to door communication components.
- Power supply to the colour camera in large properties.
- Power supply to the call-button illumination in large properties.
- Supply of Keyless In keypad.

Technical data

Rated voltage	
- Primary:	AC 230 V, 50/60 Hz
Secondary rated voltage	
- Secondary:	DC 24 V
Secondary rated current:	0.3 A
Fuse:	Fine wire fuse 250 V, T 125 mA
Ambient temperature:	-5 °C to +40 °C
Protection class:	IP 20

Dimensions

Modular width (MW):	4
---------------------	---