









Continuous controller with button interface, 4-gang for KNX



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	2100 01	1	317.84	06	4010337048022
 pure white glossy	2100 03	1	317.84	06	4010337048039
 pure white matt	2100 27	1	317.84	06	4010337048060
 anthracite	2100 28	1	320.21	06	4010337048077
 colour aluminium	2100 26	1	324.06	06	4010337048053
 black matt	2100 005	1	324.06	06	4010337037255
 grey matt	2100 015	1	324.06	06	4010337083016
 stainless steel	2100 600	1	330.84	06	4010337021520

Features

- The setpoint value is changed using the adjustment dial.
- A presence button is used to switch between Comfort and Standby mode.
- The current statuses are displayed on the continuous controller by LEDs.

Technical data

Installation depth: 23 mm

Connection cross section
- J-Y(St)Y: $2 \times 2 \times 0.8 \text{ mm}^2$
