










Speaker for the RDS flush-mounted radio



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	2282 01	1	28.22	03	4010337076230
 pure white glossy	2282 03	1	28.22	03	4010337076247
 pure white matt	2282 27	1	28.22	03	4010337076254
 anthracite	2282 28	1	29.80	03	4010337076261
 colour aluminium	2282 26	1	32.19	03	4010337076162
 black glass finish	2282 05	1	36.68	03	4010337889182
 black matt	2282 005	1	32.19	03	4010337037286
 grey matt	2282 015	1	32.19	03	4010337083931
 stainless steel	2282 600	1	36.68	03	4010337032861

Features

- Speaker for connection to the Gira RDS flush-mounted radio.

Technical data

Installation depth:	32 mm
Connections	
- Speaker/AUX connection:	1.5 mm ²
Ambient temperature:	-5 °C to +50 °C
