



LED orientation light 230 V~ white



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 White	2361 00	1	85.60	02	4010337084907
 Warm white	2364 00	1	85.60	02	4010337121749

Features

- LED orientation light for use in the private and commercial sectors.
- The orientation light is used, for example, to illuminate stairs or as an orientation aid in dark rooms.
- The brightness of the light can be set individually.
- A film which can be inscribed individually can be laid in the cover plate.
- Pictograms for room and route marking can be inserted.

Technical data

Rated voltage:	AC 230 V, 50 Hz
Power consumption:	1.7 W/8.5 VA
Brightness range:	3 to 100 %
Number of LEDs:	4
Colour temperature	
- White:	Approx. 5000 K
Installation depth:	30 mm
Connection cross section	
- maximum:	1.5 mm ²
Ambient temperature:	0 °C to +40 °C

Notes

- Professional inscription by the Gira inscription service www.marking.gira.com.
