


## LED orientation light 230 V~, white



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	2361 00	1	77.49	02	4010337084907

### Features

- LED orientation light for private and commercial use.
- The orientation light is used, for example, to illuminate stairs or as an orientation aid in dark rooms.
- The brightness of the light can be set individually.
- A film which can be inscribed individually can be laid in the cover plate.
- Pictograms for room and route marking can be inserted.

### Technical data

Rated voltage:	AC 230 V, 50 Hz
Power consumption:	1.7 W/8.5 VA
Light intensity (white):	2.2 cd
Installation depth:	30 mm
Connections	
- maximum:	1.5 mm <sup>2</sup>
Ambient temperature:	-15 °C to +40 °C

### Notes

- Professional labelling with the Gira Inscription Service [www.marking.gira.com](http://www.marking.gira.com).