




**Insert for USB power supply, 2-gang
Type A / type C**

| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  white | 2349 00 | 1/5 | 02 | 4010337104681 |
|  black | 2369 00 | 1/5 | 02 | 4010337075905 |

Features

- Charging option for up to two end devices simultaneously using USB cable type A and type C.
- Suitable as a charging device, e.g. for mobile telephones and similar devices.

Technical data

| | |
|----------------------|--------------------------|
| Charging current: | max. 3 A |
| Rated voltage | |
| - Primary: | AC 100 – 240 V, 50/60 Hz |
| - Secondary: | 5 V (± 5%) |
| Standby: | ≤ 0.15 W |
| Installation depth: | 32 mm |
| Ambient temperature: | +10 °C to +40 °C |
| Efficiency: | ≥ 75% |
| Standard-compliant: | DIN EN 60950-1/A2 |

Scope of supply

- USB cables are not included in the scope of supply.