


## Compensation module LED



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	2375 00	1/5	30.37	02	4010337031369

## Features

- Enables dimmable HV LED lamps to be operated together with Gira Tronic dimmers or Gira universal dimmers.
- Prevents HV LED lamps in leading edge Gira Tronic and Gira universal dimmers, and in switches with a lighting element of up to 3 mA, from glowing when switched off.
- Improves the dimming behaviour of HV LED lamps in trailing edge Gira Tronic and Gira universal dimmers.

## Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Power loss:	max. 2 W
Housing temperature:	max. +65 °C (tc)
Cable length:	approx. 15 cm

## Notes

- Can also be used for the dimmers already installed by the customer 0305 00 and 2390 00.

## Dimensions in mm

B 43	H 11,5	T 28,5
------	--------	--------