


Network connection box insert cat.6A, 2-gang Insulation displacement contact technology



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	2452 00	1	35.16	01	4010337881797

Features

- Shielded network connection box cat.6A with two connection sockets RJ45 (8/8) for data transfer rates up to 10 Gigabit Ethernet in accordance with IEEE 802.3an.
- 45° angled socket outlet for parapet duct, floor tank and flush-mounted installation.
- Cable entry possible from all directions in 8 x 45° increments.

Technical data

Installation depth: 33 mm.

Notes

- For screw mounting only.