


## Network connection box insert cat.6A, 2-gang Insulation displacement connectors



| Specification  | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|--|-----------|--------------|------------------------|----|---------------|
|  | 2452 00   | 1            | 36.71                  | 01 | 4010337881797 |

### Features

- Shielded network connection box cat.6A with two RJ45 jacks (8/8) for data transfer rates up to 10 Gbit-Ethernet in accordance with IEEE 802.3an.
- 45° angled socket outlet for parapet trunking, floor tank and flush-mounted installation.
- Cable entry possible from all directions in 8 x 45° increments.

### Technical data

Installation depth: 33 mm

### Notes

- For screw attachment only.