

## Bluetooth® wall transmitter, 1-gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	2461 01	1	92.66	02	4010337110712
 pure white glossy	2461 03	1	92.66	02	4010337101598
 pure white matt	2461 27	1	92.66	02	4010337101604
 anthracite	2461 28	1	94.80	02	4010337101611
 colour aluminium	2461 26	1	98.03	02	4010337101628
 black matt	2461 005	1	98.03	02	4010337101635
 grey matt	2461 015	1	98.03	02	4010337110729

### Features

- Wireless transmitter for transmitting switching, dimming or blind commands to the Bluetooth® wireless receivers from the System 3000 or third parties, e.g Casambi.

- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.
  - Configuration via the app or NFC.
- 

## Technical data

Wireless frequency:	2.402 - 2.480 GHz
Wireless protocol:	Bluetooth® low energy (BLE)
Interface:	NFC
Range	
- in free field:	up to 75 m
- in buildings:	approx. 10 m
Ambient temperature:	-25 °C to +65 °C
Humidity:	0 to 95 % (without condensation)

---

## Notes

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
  - This product cannot be used with eNet.
- 

## Scope of supply

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.
-