


Stainless steel video door station 4-gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 stainless steel	2554 20	1	1,518.92	20	4010337051251

Features

- Extension of the stainless steel door station with a video camera.

Camera

- Automatic day or night switching: the camera switches from day mode (colour display) to night mode (black and white display) and back again at a defined ambient brightness. Due to the high degree of light sensitivity in night mode, good presentation results are achieved even in poor lighting conditions.
- LEDs ensure steady illumination of the field of view at close proximity in night mode.
- Camera can be manually swivelled 20° horizontally and vertically. In combination with the wide-angle lens, a very wide field of view results.
- Automatic background lighting compensation.
- Automatic white balance.
- Automatic gain control (AGC).
- Integrated camera heating with temperature detection.
- Sprayed-water proof cover plate.
- Camera cover plate made of shock-resistant plastic. Easy to replace if damaged, e.g. due to vandalism.

Technical data

Image recording element:	CCD sensor 0.85 cm (1/3")
Wide-angle lens:	150°
Visible detection range:	100°
Area of detection (for 20° swivelling):	140°
Colour system:	PAL
Pixels:	500 (H) x 582 (V)
Horizontal resolution:	380 TV lines
Switchover threshold for colour to B/W operation:	1 lux

Light sensitivity in B/W operation:	0.1 lux
Electronic shutter speed:	up to 1/100000 s
IR filter:	integrated
Recommended mounting height for camera:	1.50 m

Notes

- The stainless steel video door station is supplied ready for connection including built-in speaker and, for larger buildings, including an add-on module. This eliminates time-consuming cabling of the call buttons. Only a Gira 2-wire bus is required to connect the door station stainless steel.

Dimensions in mm

Front plate, 1-gang:	W 160	H 285	D -
Front plate, 2-gang:	W 160	H 285	D -
Front plate, 3-gang:	W 160	H 352	D -
Front plate, 4-gang:	W 160	H 352	D -
Front plate, 6-gang:	W 160	H 437	D -
Front plate, 8-gang:	W 160	H 437	D -
Front plate, 9-gang:	W 160	H 437	D -
Flush-mounted box, 1-gang:	W 140	H 265	D 60
Flush-mounted box, 2-gang:	W 140	H 265	D 60
Flush-mounted box, 3-gang:	W 140	H 332	D 60
Flush-mounted box, 4-gang:	W 140	H 332	D 60
Flush-mounted box, 6-gang:	W 140	H 417	D 60
Flush-mounted box, 8-gang:	W 140	H 417	D 60
Flush-mounted box, 9-gang:	W 140	H 417	D 60
Name plate:	W 62	H 18	D -
