








**British Standard socket outlet (BS 1363-2) 13 A 250 V~ with shutter  
System 55**



| Specification   | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|---|-----------|--------------|------------------------|----|---------------|
|  cream white glossy           | 2776 01   | 10           | 15.74                  | 29 | 4010337079347 |
|  pure white glossy           | 2776 03   | 10           | 15.74                  | 29 | 4010337079354 |
|  anthracite                  | 2776 28   | 10           | 18.03                  | 29 | 4010337079378 |
|  colour aluminium            | 2776 26   | 10           | 21.55                  | 29 | 4010337079361 |
|  black matt                  | 2776 005  | 10           | 21.55                  | 29 | 4010337037774 |
|  grey matt                   | 2776 015  | 10           | 21.55                  | 29 | 4010337086352 |
|  stainless steel (lacquered) | 2776 600  | 10           | 24.77                  | 29 | 4010337022077 |

**Features**

- With screw terminals.

- For screw attachment only.

---

## Technical data

Installation depth: 17 mm

Connection cross section  
- maximum: 2 x 4 mm<sup>2</sup>

---