








**British Standard double socket outlet (BS 1363-2) 13 A 250 V~ with shutter**  
**Support ring 80 x 132 mm**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	2782 01	5	16.91	29	4010337079729
 pure white glossy	2782 03	5	16.91	29	4010337079736
 anthracite	2782 28	5	19.09	29	4010337079750
 colour aluminium	2782 26	5	22.41	29	4010337079743
 black matt	2782 005	5	12.90	11	4010337036470
 grey matt	2782 015	5	17.06	11	4010337086413
 stainless steel (lacquered)	2782 600	5	16.27	29	4010337022138

## Features

- With screw terminals.

- For screw attachment only.

---

## Technical data

Installation depth: 20 mm

Connection cross section  
- maximum:  $2 \times 4 \text{ mm}^2 + 2.5 \text{ mm}^2$

---