








British Standard double socket outlet (BS 1363-2) 13 A 250 V~ switched, with shutter
Support ring 80 x 132 mm



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	2783 01	5	18.41	29	4010337079798
 pure white glossy	2783 03	5	18.41	29	4010337079804
 anthracite	2783 28	5	20.59	29	4010337079828
 colour aluminium	2783 26	5	23.87	29	4010337079811
 black matt	2783 005	5	13.75	11	4010337036494
 grey matt	2783 015	5	18.16	11	4010337086420
 stainless steel (lacquered)	2783 600	5	17.23	29	4010337022145

Features

- With screw terminals.

- For screw attachment only.

Technical data

Installation depth: 20 mm
