






British Standard double socket outlet (BS 1363-2) 13 A 250 V~ switched, with control light and shutter
Support ring 80 x 132 mm



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	2784 01	5	23.51	29	4010337079859
 pure white glossy	2784 03	5	23.51	29	4010337079866
 anthracite	2784 28	5	25.76	29	4010337079880
 colour aluminium	2784 26	5	29.14	29	4010337079873
 black matt	2784 005	5	16.79	11	4010337036487
 grey matt	2784 015	5	22.19	11	4010337086758
 stainless steel (lacquered)	2784 600	5	20.66	29	4010337022176

Features

- With screw terminals.

- For screw attachment only.

Technical data

Installation depth: 20 mm
