







British Standard Fused spur connection unit (BS 1363-4) 13 A 250 V~ switched System 55



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	2785 01	1/5	19.68	29	4010337079910
 pure white glossy	2785 03	1/5	19.68	29	4010337079927
 anthracite	2785 28	1/5	21.85	29	4010337079941
 colour aluminium	2785 26	1/5	25.16	29	4010337079934
 black matt	2785 005	1/5	14.49	29	4010337037101
 grey matt	2785 015	1/5	19.15	29	4010337086994

Features

- With screw terminals.
- For screw attachment only.

Technical data

Installation depth:	29 mm
Connection cross section - maximum:	2 x 2.5 mm ²

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com
