





**British Standard rocker switch (BS EN 60669-1) 3-gang with rockers
System 55, 1-way switch**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	2830 01	10	21.65	29	4010337830016
 pure white glossy	2830 03	10	21.65	29	4010337830030
 anthracite	2830 28	10	23.84	29	4010337830283
 colour aluminium	2830 26	10	27.12	29	4010337830269
 black matt	2830 005	10	27.12	29	4010337038580
 grey matt	2830 015	10	27.12	29	4010337087113
 stainless steel (lacquered)	2830 600	10	30.16	29	4010337022022

Technical data

Installation depth:	25 mm
Connection cross section - for conductors up to:	2.5 mm ²
Rated output:	100 W LED load (IEC 60669)

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com
