





**British Standard rocker switch (BS EN 60669-1) 3-gang with rockers
System 55, 1-way switch**



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|---|-----------|--------------|------------------------|----|---------------|
|  cream white glossy | 2830 01 | 10 | 21.65 | 29 | 4010337830016 |
|  pure white glossy | 2830 03 | 10 | 21.65 | 29 | 4010337830030 |
|  anthracite | 2830 28 | 10 | 23.84 | 29 | 4010337830283 |
|  colour aluminium | 2830 26 | 10 | 27.12 | 29 | 4010337830269 |
|  black matt | 2830 005 | 10 | 27.12 | 29 | 4010337038580 |
|  grey matt | 2830 015 | 10 | 27.12 | 29 | 4010337087113 |
|  stainless steel (lacquered) | 2830 600 | 10 | 30.16 | 29 | 4010337022022 |

Technical data

| | |
|---|----------------------------|
| Installation depth: | 25 mm |
| Connection cross section - for conductors up to: | 2.5 mm ² |
| Rated output: | 100 W LED load (IEC 60669) |

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com
