

**British Standard rocker button (BS EN 60669-1), 3-gang 10 A 250 V~ with rockers  
System 55, NO contact 1-pole**



| Specification   | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|---|-----------|--------------|------------------------|----|---------------|
|  cream white glossy           | 2844 01   | 10           | 32.27                  | 29 | 4010337082033 |
|  pure white glossy           | 2844 03   | 10           | 32.27                  | 29 | 4010337082040 |
|  anthracite                  | 2844 28   | 10           | 34.61                  | 29 | 4010337082064 |
|  colour aluminium            | 2844 26   | 10           | 38.06                  | 29 | 4010337082057 |
|  black matt                  | 2844 005  | 10           | 38.06                  | 29 | 4010337037903 |
|  grey matt                   | 2844 015  | 10           | 38.06                  | 29 | 4010337087182 |
|  stainless steel (lacquered) | 2844 600  | 10           | 41.33                  | 29 | 4010337021957 |

## Features

- With screw terminals.

## Technical data

Installation depth: 25 mm

Connection cross section  
- for conductors up to: 2.5 mm<sup>2</sup>

---

## Notes

- For screw attachment only.

---