








**British Standard rocker button (BS EN 60669-1), 3-gang 10 A 250 V~ with rockers
System 55, NO contact 1-pole**



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 2844 01 | 10 | 29 | 4010337082033 |
|  pure white glossy | 2844 03 | 10 | 29 | 4010337082040 |
|  anthracite | 2844 28 | 10 | 29 | 4010337082064 |
|  colour aluminium | 2844 26 | 10 | 29 | 4010337082057 |
|  black matt | 2844 005 | 10 | 29 | 4010337037903 |
|  grey matt | 2844 015 | 10 | 29 | 4010337087182 |
|  stainless steel (lacquered) | 2844 600 | 10 | 29 | 4010337021957 |

Features

- With screw terminals.

Technical data

Installation depth: 25 mm

Connection cross section
- for conductors up to: 2.5 mm²

Notes

- For screw attachment only.
