








**British Standard rocker button (BS EN 60669-1), 3-gang 10 A 250 V~ with rockers
System 55, NO contact 1-pole**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	2844 01	10	32.27	29	4010337082033
 pure white glossy	2844 03	10	32.27	29	4010337082040
 anthracite	2844 28	10	34.61	29	4010337082064
 colour aluminium	2844 26	10	38.06	29	4010337082057
 black matt	2844 005	10	38.06	29	4010337037903
 grey matt	2844 015	10	38.06	29	4010337087182
 stainless steel (lacquered)	2844 600	10	41.33	29	4010337021957

Features

- With screw terminals.

Technical data

Installation depth: 25 mm

Connection cross section
- for conductors up to: 2.5 mm²

Notes

- For screw attachment only.
